

**Conductor markers  
CLI C 3-6 GE/SW 2 MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |                                                                          |
|------------|--------------------------------------------------------------------------|
| Type       | CLI C 3-6 GE/SW 2 MP                                                     |
| Order No.  | <a href="#">0253411508</a>                                               |
| Version    | Conductor markers, 6 x 11 mm, PVC, soft, without Cadmium, Colour: Yellow |
| GTIN (EAN) | 4008190028145                                                            |
| Qty.       | 20 pc(s).                                                                |

## Conductor markers CLI C 3-6 GE/SW 2 MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |       |       |
|------------|--------|-------|-------|
| Length     | 6 mm   | Width | 11 mm |
| Height     | 17 mm  | Depth | 17 mm |
| Net weight | 0.72 g |       |       |

### General data

|                                              |             |                                   |                            |
|----------------------------------------------|-------------|-----------------------------------|----------------------------|
| Colour                                       | Yellow      | Colour of printing                | Black                      |
| Insulation cross-section, max.               | 16 mm       | Material                          | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4           | Operating temperature range, max. | 80 °C                      |
| Operating temperature range, min.            | -30 °C      | Orientation of print              | horizontal                 |
| Printed characters                           | Numbers     | Printing                          | 2                          |
| Printing method                              | Laser print | Type of printing                  | Standard                   |
| UL 94 flammability rating                    | V-0         |                                   |                            |

### Conductor and cable markers

|                               |                    |                               |                    |
|-------------------------------|--------------------|-------------------------------|--------------------|
| Conductor O.D., max.          | 16 mm              | Conductor O.D., min.          | 8 mm               |
| Conductor cross-section, max. | 70 mm <sup>2</sup> | Conductor cross-section, min. | 16 mm <sup>2</sup> |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Conductor markers CLI C 3-6 GE/SW 2 MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen



Product is similar to illustration