

**Conductor markers
CLI C 1-3 RT/SW + MP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Type	CLI C 1-3 RT/SW + MP
Order No.	0252611737
Version	Conductor markers, 3 x 4.2 mm, PVC, soft, without Cadmium, Colour: Red
GTIN (EAN)	4008190115944
Qty.	200 pc(s).

Conductor markers CLI C 1-3 RT/SW + MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	3 mm	Width	4.2 mm
Height	5.1 mm	Depth	5 mm
Net weight	0.06 g		

General data

Colour	Red	Colour of printing	Black
Insulation cross-section, max.	5 mm	Material	PVC, soft, without Cadmium
Material colour according to resistance code	2	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Orientation of print	horizontal
Printed characters	Symbols	Printing	+
Printing method	Laser print	Recommended industries	Process, Machinery
Type of printing	Standard	UL 94 flammability rating	V-0

Conductor and cable markers

Conductor O.D., max.	5 mm	Conductor O.D., min.	3 mm
Conductor cross-section, min.	1.5 mm ²		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Conductor markers CLI C 1-3 RT/SW + MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen



Product is similar to illustration