

**Conductor markers  
CLI O 30-3 GE/SW O MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers.

**Advantages:**

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

**General ordering data**

Type	CLI O 30-3 GE/SW O MP
Order No.	<a href="#">0648201665</a>
Version	Conductor markers, 3 x 6 mm, PVC, soft, without Cadmium, Colour: Yellow
GTIN (EAN)	4008190179397
Qty.	200 pc(s).

## Conductor markers CLI O 30-3 GE/SW O MP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	3 mm	Width	6 mm
Height	5.5 mm	Depth	6 mm
Net weight	0.065 g		

### General data

Colour	Yellow	Colour of printing	Black
Material	PVC, soft, without Cadmium	Material colour according to resistance code	4
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Upper-case letters
Printing	O	Printing method	Laser print
Type of printing	Standard	UL 94 flammability rating	V-0

### Conductor and cable markers

Conductor O.D., max.	5 mm	Conductor O.D., min.	4 mm
Conductor cross-section, max.	4 mm <sup>2</sup>	Conductor cross-section, min.	3 mm <sup>2</sup>

### Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

### Approvals

Approvals	
ROHS	Conform

**Datenblatt**

**Conductor markers**  
**CLI O 30-3 GE/SW O MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Product is similar to illustration