

**SAK Series, Accessories  
AD 250**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



As protection against contact, dust and moisture, Weidmüller can provide cover profiles which are used, for example, in signal or lighting pole distribution. Weidmüller can supply terminal strips ready assembled and labelled to meet your specifications.

**General ordering data**

|            |  |
|------------|--|
| Type       | AD 250                                     |
| Order No.  | <a href="#">0634100000</a>                 |
| Version    | SAK Series, Accessories, Hood, Transparent |
| GTIN (EAN) | 4008190083199                              |
| Qty.       | 10 pc(s).                                  |

**Datenblatt**

**SAK Series, Accessories  
AD 250**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

|            |        |        |         |
|------------|--------|--------|---------|
| Length     | 70 mm  | Height | 49.5 mm |
| Net weight | 75.9 g |        |         |

**Temperatures**

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature            |        | Storage temperature              |        |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |

**Additional technical data**

|                     |                 |         |                            |
|---------------------|-----------------|---------|----------------------------|
| Installation advice | Direct mounting | Version | End and intermediate plate |
|---------------------|-----------------|---------|----------------------------|

**Dimensions**

|              |       |              |       |
|--------------|-------|--------------|-------|
| TS 32 offset | 35 mm | TS 35 offset | 35 mm |
|--------------|-------|--------------|-------|

**Material data**

|        |             |                           |     |
|--------|-------------|---------------------------|-----|
| Colour | Transparent | UL 94 flammability rating | V-2 |
|--------|-------------|---------------------------|-----|

**System specifications**

|                |                         |
|----------------|-------------------------|
| Product family | SAK Series, Accessories |
|----------------|-------------------------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000886    | UNSPSC     | 30-21-18-27 |
| eClass 5.1 | 27-14-11-33 | eClass 6.2 | 27-14-11-33 |
| eClass 7.1 | 27-14-11-33 |            |             |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|