

**Conductor markers**  
**CLI O 10-3 GE/SW K MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



CLI O conductor markers are fitted to connected conductors, and are therefore suitable for updating existing systems. Without problems, three different sizes can be used for marking conductor cross-sections from 0.4 mm<sup>2</sup> to max. 4.0 mm<sup>2</sup>. The shape and design guarantee secure and permanent attachment of the individually combinable markers.

**Advantages:**

- Open markers for connected conductors
- Marker version with anti-rotation safeguard for secure combination marking
- Perfect for any supplementary labelling
- Extremely low space requirements
- Rapid clip-on attachment saves time

**General ordering data**

|            |                                                                         |
|------------|-------------------------------------------------------------------------|
| Type       | CLI O 10-3 GE/SW K MP                                                   |
| Order No.  | <a href="#">0648001657</a>                                              |
| Version    | Conductor markers, 3 x 4 mm, PVC, soft, without Cadmium, Colour: Yellow |
| GTIN (EAN) | 4008190172893                                                           |
| Qty.       | 200 pc(s).                                                              |

## Conductor markers CLI O 10-3 GE/SW K MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |       |      |
|------------|---------|-------|------|
| Length     | 3 mm    | Width | 4 mm |
| Height     | 3.5 mm  | Depth | 4 mm |
| Net weight | 0.035 g |       |      |

### General data

|                                   |                            |                                              |                    |
|-----------------------------------|----------------------------|----------------------------------------------|--------------------|
| Colour                            | Yellow                     | Colour of printing                           | Black              |
| Material                          | PVC, soft, without Cadmium | Material colour according to resistance code | 4                  |
| Operating temperature range, max. | 80 °C                      | Operating temperature range, min.            | -30 °C             |
| Orientation of print              | horizontal                 | Printed characters                           | Upper-case letters |
| Printing                          | K                          | Printing method                              | Laser print        |
| Type of printing                  | Standard                   | UL 94 flammability rating                    | V-0                |

### Conductor and cable markers

|                               |                     |                               |                     |
|-------------------------------|---------------------|-------------------------------|---------------------|
| Conductor O.D., max.          | 3 mm                | Conductor O.D., min.          | 2 mm                |
| Conductor cross-section, max. | 1.5 mm <sup>2</sup> | Conductor cross-section, min. | 0.4 mm <sup>2</sup> |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Conductor markers CLI O 10-3 GE/SW K MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen



Product is similar to illustration