

Office VOIP
Home Office VOIP
Meeting Rooms VOIP
Distance Learning VOIP

- Plug and play via 3,5 mm stereo jack
- Omnidirectional capsule
- Cascadable for multi-person use (up to 5 units)
- Wide frequency range



CBL 410 PCC black

CBL 410 PCC white

The AKG CBL 410 PCC is a simple to use, plug and play desktop microphone for use with any PC or Laptop. It improves audio quality incredibly when making a conference via VOIP. The microphone reproduces the voice with a clear and natural sound.

With its 3,5 mm stereo jack it is a 100% plug and play device. No drivers are needed.


Its ability to be cascaded makes the CBL 410 PCC the perfect tool for modern communication for both single person use in the office and/or multi-person use in a modern meeting room.

This microphone provides optimum intelligibility and audio quality for your meetings.

The CBL 410 PCC is also an excellent choice for recording applications.




In the multi-person application up to 4 microphones can be cascaded and enable a clear conference. Just connect the second microphone to the IN-jack of the first microphone, the third microphone to the second one, and so on.



TECHNICAL SPECIFICATIONS

Type	condenser permanent load, omnidirectional
Sensitivity	3,88mV/Pa (-48dBV)
Frequency Range	20-20,000 Hz
Impedance	2000 ohms
Finish	white / black
Cable	100 cm (39.4 in.)
Connectors	3,5 mm stereo jack 3,5 mm plug
Supply Voltage	1,5 – 5 volts
Maximum Current Consumption	0,5 mA
S/N ratio	58 dBA
Max. SPL for 1% THD	120 dB
Dimensions	114 x 114 x 21 mm (4.5 x 4.5 x 0.8 in.)
Net / Shipping Weight	159 / 222 g (5.6 / 7.8 oz.)
Masterpack Quantity	80 (2 inner boxes with 40 units each)
Masterpack Size	580 x 560 x 240 mm (22.8 x 22 x 9.5 in.)
Masterpack Net / Shipping Weight	17 / 18,5 kg (37.5 / 40.8 lbs.)
Item Number	black: 3177H00010 white: 3177H00020



www.akg.com

AKG Acoustics GmbH

Lemböckgasse 21–25, 1230 Vienna/AUSTRIA, phone: + 43 1 86654 0

e-mail: sales@akg.com

AKG Acoustics, U.S.

8400 Balboa Boulevard, Northridge, CA 91329, U.S.A., phone: + 1 818 920 3212

e-mail: akgusa@harman.com

For other products and distributors worldwide visit www.akg.com

Specifications subject to change without notice.



by **HARMAN**