CH20M AD SHL 5.00/04 BK



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com





The new standard for integrating innovative electronics on the DIN rail.

Trend-setting flexibility and design freedom. Flexibility, efficiency, functionality and security.

CH20M (Component Housing IP**20** Modular) – Weidmüller's new housing standard fits perfectly with customised electronics applications. This "standard tailormade fit" combines the design freedom made possible by a pioneering concept of modularity with the minimized overhead and optimised planning security of a standard system.

From development to production, the CH20M represents efficiency. It covers all of the requirements for a modern electronics platform built with the future in mind. The system has several outstanding features, including its scalability, flexibility, high security level and innovative application functionality. Overall, the product line covers all common pitches, from the 6.1-mm sliced design to the 22.5-mm and 67-mm large-scale housings.

The application-centred design was developed from real world experience for the real world. It is designed with the market, the application and the future in mind. The essential features speak for themselves:

- Systematic modularity- from head (plate) to (clip-on) foot
- Excellent scalability 7 different widths, from 6.1 67.5 mm!

- Maximized security: with leading-pin contact and captive coding system
- Unlimited continuity a unified design for all pitch widths
- Very compact size up to 4 connection levels and with release lever
- Complete process security SMT/THR connection components packaged in Tape-on-Reel and an optimised PCB design
- Maximized efficiency with the optimised use of PCB surface space

CH20M - offering the best performance with the least effort. A quantum leap for your application!

General ordering data

Туре	CH20M AD SHL 5.00/04 BK		
Order No.	<u>1221310000</u>		
Version	Electronics housings Black, Cover hood, Width: 22.5 mm		
GTIN (EAN)	4050118004830		
Qty.	50 pc(s).		

CH20M AD SHL 5.00/04 BK

Technische Daten



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Dimensions and weights				
Length	14.6 mm	Width	22.5 mm	
Height	23.7 mm	Net weight	2.31 g	
System characteristic	S			
Version	Cover hood	Protection degree	IP 20	
Material data				
Insulating material	PA 66 GF 30	Colour	Black	
Classifications				
eClass 6.2	27-18-08-02	eClass 7.1	27-18-27-02	
	27-10-00-02	eclass 7.1	27-18-27-02	
Approvals				
ROHS	Conform			