

**Conductor markers  
CLI C 1-3 GE/SW Z CD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|            |                                                                           |
|------------|---------------------------------------------------------------------------|
| Type       | CLI C 1-3 GE/SW Z CD                                                      |
| Order No.  | <a href="#">1568251698</a>                                                |
| Version    | Conductor markers, 3 x 4.2 mm, PVC, soft, without Cadmium, Colour: Yellow |
| GTIN (EAN) | 4008190026653                                                             |
| Qty.       | 500 pc(s).                                                                |

**Conductor markers  
CLI C 1-3 GE/SW Z CD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technische Daten****Dimensions and weights**

|            |         |       |        |
|------------|---------|-------|--------|
| Length     | 3 mm    | Width | 4.2 mm |
| Height     | 5.1 mm  | Depth | 5 mm   |
| Net weight | 0.084 g |       |        |

**General data**

|                                   |                            |                                              |                    |
|-----------------------------------|----------------------------|----------------------------------------------|--------------------|
| Colour                            | Yellow                     | Colour of printing                           | Black              |
| Material                          | PVC, soft, without Cadmium | Material colour according to resistance code | 4                  |
| Operating temperature range, min. | -30 °C                     | Orientation of print                         | horizontal         |
| Printed characters                | Upper-case letters         | Printing                                     | Z                  |
| Printing method                   | Laser print                | Recommended industries                       | Process, Machinery |
| Type of printing                  | Standard                   | UL 94 flammability rating                    | V-0                |

**Conductor and cable markers**

|                               |                     |                               |                   |
|-------------------------------|---------------------|-------------------------------|-------------------|
| Conductor O.D., max.          | 5 mm                | Conductor cross-section, max. | 4 mm <sup>2</sup> |
| Conductor cross-section, min. | 1.5 mm <sup>2</sup> |                               |                   |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

**Approvals**

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Conductor markers CLI C 1-3 GE/SW Z CD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen



Product is similar to illustration