

**Accessories**  
**WKS 1/3**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Product image****Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

**General ordering data**

|            |                                                                                    |
|------------|------------------------------------------------------------------------------------|
| Type       | WKS 1/3                                                                            |
| Order No.  | <a href="#">1604290000</a>                                                         |
| Version    | Accessories, Cross-connection slider, Cross-connector accessories, No. of poles: 3 |
| GTIN (EAN) | 4008190164027                                                                      |
| Qty.       | 50 pc(s).                                                                          |

## Accessories

### WKS 1/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Width      | 6.1 mm  | Width (inches)  | 0.24 inch  |
| Height     | 22 mm   | Height (inches) | 0.866 inch |
| Depth      | 18.8 mm | Depth (inches)  | 0.74 inch  |
| Net weight | 2.22 g  |                 |            |

### Temperatures

|                                   |        |                                  |        |
|-----------------------------------|--------|----------------------------------|--------|
| Operating temperature range, max. | 100 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max.  | 100 °C |                                  |        |

### Material data

|                           |              |        |        |
|---------------------------|--------------|--------|--------|
| Material                  | Polyamide 66 | Colour | orange |
| UL 94 flammability rating | V-2          |        |        |

### System specifications

|         |                             |
|---------|-----------------------------|
| Version | Cross-connector accessories |
|---------|-----------------------------|

### Additional technical data

|                     |                 |                |         |
|---------------------|-----------------|----------------|---------|
| Installation advice | Direct mounting | Type of fixing | Plugged |
| Type of mounting    | Clamped         |                |         |

### Dimensions

|                 |         |
|-----------------|---------|
| Pitch in mm (P) | 14.1 mm |
|-----------------|---------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000761    | ETIM 4.0   | EC000489    |
| ETIM 5.0   | EC000489    | ETIM 6.0   | EC000489    |
| UNSPSC     | 30-21-18-01 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 | eClass 8.1 | 27-14-11-40 |
| eClass 9.0 | 27-14-11-40 | eClass 9.1 | 27-14-11-40 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                          |
|--------------------|------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a>      |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a> |
| Engineering Data   | <a href="#">STEP</a>                     |