

## Device markers ESG 8/17 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

### General ordering data

Type	ESG 8/17 MC NE WS
Order No.	<a href="#">1674740000</a>
Version	Device markers, MultiCard, 17 x 8 mm, Polyamide 66, Colour: White, pluggable
GTIN (EAN)	4008190447663
Qty.	200 pc(s).

## Datenblatt

### Device markers ESG 8/17 MC NE WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	17 mm	Width	8 mm
Height	0.8 mm	Net weight	0.515 g

### General data

Application/manufacture	Telemecanique	Colour	White
Material	Polyamide 66	Material colour according to resistance code	9
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-2		

### Classifications

ETIM 3.0	EC001288	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-29	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

### Approvals

Approvals	
ROHS	Conform

### Downloads

M-Print® PRO configuration file [mc\\_esg\\_8\\_17\\_mcf.zip](#)

**Datenblatt**

**Device markers**  
**ESG 8/17 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Zeichnungen**

**Example of use**



**Drawing**

