

SKMU MS (brass locknut)
SKMU M32 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

General ordering data

Type	SKMU M32 MS
Order No.	1737020000
Version	SKMU MS (brass locknut), Locknut, M 32, 4 mm, Brass, nickel-plated
GTIN (EAN)	4008190956493
Qty.	100 pc(s).

SKMU MS (brass locknut)
SKMU M32 MS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Net weight 2.12 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Width

Thickness 3.5 mm

General information

AF size 1	36 mm	Cable glands	metric
External thread	M 32	Internal thread	M 32
Length of thread	4 mm	Material	Brass, nickel-plated
O.D.	41.58 mm	Pitch of thread	1.5 mm
Thickness	3.5 mm		

Classifications

ETIM 3.0	EC000940	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000940
UNSPSC	30-21-18-01	eClass 5.1	23-11-07-01
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-24
eClass 9.1	27-14-44-24		

Approvals

ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP

Data sheet**SKMU MS (brass locknut)
SKMU M32 MS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings