

Z-series, Accessories
ZQV 1.5N/R3.5/10 GE**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Weidmüller offers users of modular terminals of the Z-Series a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

The accessories must comply with the same quality standards as the modular terminals themselves.

General ordering data

| | |
|------------|---|
| Type | ZQV 1.5N/R3.5/10 GE |
| Order No. | 1754290000 |
| Version | Z-series, Accessories, Cross-connector, For the terminals, No. of poles: 10 |
| GTIN (EAN) | 4032248027415 |
| Qty. | 20 pc(s). |

Z-series, Accessories ZQV 1.5N/R3.5/10 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|--------|----------|------------|--------|
| Length | 34.1 mm | Width | 2.4 mm |
| Height | 12.15 mm | Net weight | 1.95 g |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature | | Storage temperature | |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Additional technical data

| | | | |
|--------------------------|----|---------|-------------------|
| Explosion-tested version | No | Version | For the terminals |
|--------------------------|----|---------|-------------------|

Rated data

| | |
|---------------|--------|
| Rated current | 17.5 A |
|---------------|--------|

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Material | Wemid | Colour | Yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|----------------|-----------------------|
| Product family | Z-series, Accessories |
|----------------|-----------------------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000489 | UNSPSC | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 | | |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|