

**Z-series  
ZAP ZDU4/NT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



Weidmüller offers users of modular terminals of the Z-Series a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

The accessories must comply with the same quality standards as the modular terminals themselves.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | ZAP ZDU4/NT                |
| Order No.  | <a href="#">1757970000</a> |
| Version    | Z-series, End plate        |
| GTIN (EAN) | 4008190121501              |
| Qty.       | 20 pc(s).                  |

## Z-series ZAP ZDU4/NT

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |          |            |         |
|--------|----------|------------|---------|
| Length | 76.35 mm | Width      | 1.5 mm  |
| Height | 37.52 mm | Net weight | 4.259 g |

### Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature            |        | Storage temperature              |        |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

### Additional technical data

|                     |                 |         |           |
|---------------------|-----------------|---------|-----------|
| Installation advice | Direct mounting | Version | End plate |
|---------------------|-----------------|---------|-----------|

### Dimensions

|              |       |
|--------------|-------|
| TS 15 offset | 17 mm |
|--------------|-------|

### Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | Dark Beige |
| UL 94 flammability rating | V-0   |        |            |

### System specifications

|                |          |
|----------------|----------|
| Product family | Z-series |
|----------------|----------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000886    | UNSPSC     | 30-21-18-27 |
| eClass 5.1 | 27-14-11-33 | eClass 6.2 | 27-14-11-33 |
| eClass 7.1 | 27-14-11-33 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|