

**Device markers  
ETO SM 27/18 TRANSPAR.**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet PRO, MCP Plus plotter, MCP Basic or MC-Mobilo marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**General ordering data**

|            |                                                                            |
|------------|----------------------------------------------------------------------------|
| Type       | ETO SM 27/18 TRANSPAR.                                                     |
| Order No.  | <a href="#">1720590002</a>                                                 |
| Version    | Device markers, MultiCard, 18 x 27 mm, Polyester film, Colour: Transparent |
| GTIN (EAN) | 4008190988005                                                              |
| Qty.       | 10 pc(s).                                                                  |

## Device markers ETO SM 27/18 TRANSPAR.

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |        |            |        |
|--------|--------|------------|--------|
| Length | 18 mm  | Width      | 27 mm  |
| Height | 0.2 mm | Net weight | 12.5 g |

### General data

|                                   |                             |                                   |             |
|-----------------------------------|-----------------------------|-----------------------------------|-------------|
| Adhesive                          | Permanent acrylic copolymer | Colour                            | Transparent |
| Material                          | Polyester film              | Number per sheet                  | 112         |
| Operating temperature range, max. | 80 °C                       | Operating temperature range, min. | -20 °C      |
| UL 94 flammability rating         | HB                          |                                   |             |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001288    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-91-29 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |