

**Accessories**  
**ZVQ 2.5/1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



Weidmüller offers users of modular terminals of the Z-Series a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

The accessories must comply with the same quality standards as the modular terminals themselves.

**General ordering data**

|            |                                                                  |
|------------|------------------------------------------------------------------|
| Type       | ZVQ 2.5/1.5                                                      |
| Order No.  | <a href="#">1720700000</a>                                       |
| Version    | Accessories, Cross-connector, For the terminals, No. of poles: 1 |
| GTIN (EAN) | 4008190374006                                                    |
| Qty.       | 50 pc(s).                                                        |

**Accessories**  
**ZVQ 2.5/1.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten****Dimensions and weights**

|        |        |            |         |
|--------|--------|------------|---------|
| Length | 4.4 mm | Width      | 3 mm    |
| Height | 47 mm  | Net weight | 1.041 g |

**Temperatures**

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature            |        | Storage temperature              |        |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

**Additional technical data**

|                          |                   |                     |                 |
|--------------------------|-------------------|---------------------|-----------------|
| Explosion-tested version | No                | Installation advice | Direct mounting |
| Version                  | For the terminals |                     |                 |

**Material data**

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | Orange |
| UL 94 flammability rating | V-0   |        |        |

**System specifications**

|                |             |
|----------------|-------------|
| Product family | Accessories |
|----------------|-------------|

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 |            |             |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|