

**ClipCard
CC 15/17 MC NE WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet PRO, the MCP Plus plotter, MCP Basis and MC-Mobilo.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	CC 15/17 MC NE WS
Order No.	1876570000
Version	ClipCard, Device markers, 15 x 17 mm, Holder CC-H 15/17, white
GTIN (EAN)	4032248466481
Qty.	80 pc(s).
compatible printer	1324380000

ClipCard CC 15/17 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	17 mm	Width (inches)	0.669 inch
Height	15 mm	Height (inches)	0.591 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	1.25 g		

General data

Application/manufacturer	Holder CC-H 15/17	Colour	white
Halogen	No	Material	Polyamide 66
Material colour according to resistance code	9	Operating temperature range	-40...100 °C
Recommended industries	Machinery	UL 94 flammability rating	V-2
Width	17 mm		

Classifications

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

**ClipCard
CC 15/17 MC NE WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

