

**Z-series, Accessories**  
**ZQV 16/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



Weidmüller offers users of modular terminals of the Z-Series a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

The accessories must comply with the same quality standards as the modular terminals themselves.

**General ordering data**

|            |                                                                            |
|------------|----------------------------------------------------------------------------|
| Type       | ZQV 16/2                                                                   |
| Order No.  | <a href="#">1739690000</a>                                                 |
| Version    | Z-series, Accessories, Cross-connector, For the terminals, No. of poles: 2 |
| GTIN (EAN) | 4008190957148                                                              |
| Qty.       | 25 pc(s).                                                                  |

## Z-series, Accessories ZQV 16/2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |         |            |        |
|--------|---------|------------|--------|
| Length | 20.6 mm | Width      | 5.2 mm |
| Height | 35.1 mm | Net weight | 9.9 g  |

### Temperatures

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature            |        | Storage temperature              |        |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

### Additional technical data

|                          |    |         |                   |
|--------------------------|----|---------|-------------------|
| Explosion-tested version | No | Version | For the terminals |
|--------------------------|----|---------|-------------------|

### Rated data

|               |      |
|---------------|------|
| Rated current | 76 A |
|---------------|------|

### Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | Yellow |
| UL 94 flammability rating | V-0   |        |        |

### System specifications

|                |                       |
|----------------|-----------------------|
| Product family | Z-series, Accessories |
|----------------|-----------------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 |            |             |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|