

**W-Series, Accessories**  
**WQV 95N/120N/2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



The versatile and extensive range of products - from 0.05 mm<sup>2</sup> to 300 mm<sup>2</sup> - means that you have diverse options for your applications at your disposal.  
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

**General ordering data**

|            |                                                                            |
|------------|----------------------------------------------------------------------------|
| Type       | WQV 95N/120N/2                                                             |
| Order No.  | <a href="#">1826890000</a>                                                 |
| Version    | W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 2 |
| GTIN (EAN) | 4032248329946                                                              |
| Qty.       | 5 pc(s).                                                                   |

## W-Series, Accessories WQV 95N/120N/2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |       |            |         |
|--------|-------|------------|---------|
| Length | 37 mm | Width      | 9.5 mm  |
| Height | 29 mm | Net weight | 49.78 g |

### Temperatures

|                       |                     |
|-----------------------|---------------------|
| Operating temperature | Storage temperature |
|-----------------------|---------------------|

### Additional technical data

|                          |                   |                     |                 |
|--------------------------|-------------------|---------------------|-----------------|
| Explosion-tested version | No                | Installation advice | Direct mounting |
| Version                  | For the terminals |                     |                 |

### Rated data

|               |       |
|---------------|-------|
| Rated current | 269 A |
|---------------|-------|

### Material data

|          |       |        |      |
|----------|-------|--------|------|
| Material | Steel | Colour | Grey |
|----------|-------|--------|------|

### System specifications

|                |                       |
|----------------|-----------------------|
| Product family | W-Series, Accessories |
|----------------|-----------------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-11-40 | eClass 6.2 | 27-14-11-40 |
| eClass 7.1 | 27-14-11-40 |            |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|