

Terminal markers MFF 10/6 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



MultiFit is the Weidmüller marker system used for other makes of terminals in 4, 5, 6, 6.5, 7.5, 8, 10 and 12 mm pitches. Similar to the Weidmüller dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the SMark laser, PrintJet ADVANCED, plotter or MC-Mobilo,
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

General ordering data

Type	MFF 10/6 MC NE WS
Order No.	1856780000
Version	Terminal markers, MultiCard, 10 x 6 mm, Polyamide 66, Colour: White
GTIN (EAN)	4032248400881
Qty.	600 pc(s).

Terminal markers MFF 10/6 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	10 mm	Width	6 mm
Net weight	0.15 g		

General data

Application/manufacturer	Festo	Colour	White
Material	Polyamide 66	Material colour according to resistance code	9
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Type of printing	blank	UL 94 flammability rating	V-2

Connector markers

Pitch in mm (P)	6 mm
-----------------	------

Classifications

ETIM 3.0	EC000761	UNSPSC	30-21-18-07
eClass 5.1	27-14-11-37	eClass 6.2	27-14-11-37
eClass 7.1	27-14-11-37		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	mc_mff_10_6_mcf.zip
STEP	1856780000_36704_MFF-10x6-MC-Matte_STP.stp

Terminal markers MFF 10/6 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Example of use



Drawing

