

ESG 9/11 K MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

General ordering data

| | |
|------------|----------------------------|
| Type | ESG 9/11 K MC NE WS |
| Order No. | 1857440000 |
| GTIN (EAN) | 4032248402731 |
| Qty. | 200 pc(s). |

ESG 9/11 K MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|--------|--------|------------|--------|
| Length | 11 mm | Width | 9 mm |
| Height | 0.8 mm | Net weight | 0.45 g |

General data

| | | | |
|----------------------------------------------|----------------------------|-----------------------------------|---------------|
| Adhesive | Double-sided adhesive tape | Application/manufacturer | Self-adhesive |
| Colour | White | Material | Polyamide 66 |
| Material colour according to resistance code | 9 | Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C | UL 94 flammability rating | V-2 |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001288 | UNSPSC | 30-21-18-01 |
| eClass 5.1 | 27-14-91-29 | eClass 6.2 | 27-14-91-29 |

Approvals

| | |
|-----------|---------|
| Approvals | |
| ROHS | Conform |

ESG 9/11 K MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Example of use



Drawing

