Conductor markers
CLI C 02-3 WS/SW 0 CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Type	CLI C 02-3 WS/SW 0 CD
Order No.	1869821502
Version	Conductor markers, 3 x 3.4 mm, PVC, soft, without Cadmium, Colour: White
GTIN (EAN)	4032248446346
Qty.	500 pc(s).

Conductor markers
CLI C 02-3 WS/SW 0 CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	3 mm	Width	3.4 mm
Height	3.6 mm	Depth	3.5 mm
Net weight	0.04 g		

General data

Colour	White	Colour of printing	Black
Material	PVC, soft, without Cadmium	Material colour according to resistance code	9
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Numbers
Printing	0	Printing method	Laser print
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0		

Conductor and cable markers

Conductor O.D., max.	3 mm	Conductor O.D., min.	1 mm
Conductor cross-section, max.	1.5 mm²	Conductor cross-section, min.	0.25 mm²

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Conductor markers
CLI C 02-3 WS/SW 0 CD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen



Product is similar to illustration