

Connecting elements H2,5/17,5X BL SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



- In multi-pack bag
- Weidmüller colour code

General ordering data

Type	H2,5/17,5X BL SV
Order No.	9006670000
Version	Wire-end ferrule, insulated, 14 mm, 8 mm, blue
GTIN (EAN)	4008190332273
Qty.	100 pc(s).
Packaging	Multipack bag

Data sheet

Connecting elements H2,5/17,5X BL SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	17.5 mm	Width (inches)	0.689 inch
Net weight	0.262 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	7.6 mm	Colour code	Weidmüller
Conductor cross-section	2.5 mm ²	Contact surface diameter (D1)	2.3 mm
Contact surface length (L2)	8 mm	L1 in mm	17.5 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.3 mm
Stripping length	14 mm	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Data sheet

**Connecting elements
H2,5/17,5X BL SV**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

