

**SwitchMark
SM 27/18 MC NE RT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet PRO, MCP Plus plotter, MCP Basic or MC-Mobilo marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	SM 27/18 MC NE RT
Order No.	1906110000
Version	SwitchMark, Device markers, 18 x 27 mm, SwitchMark holder, red
GTIN (EAN)	4032248528295
Qty.	80 pc(s).
compatible printer	1324380000

SwitchMark SM 27/18 MC NE RT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	27 mm	Width (inches)	1.063 inch
Height	18 mm	Height (inches)	0.709 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	1.39 g		

General data

Application/manufacture	SwitchMark holder	Colour	red
Halogen	No	Material	Polyamide 66
Material colour according to resistance code	2	Operating temperature range	-40...100 °C
UL 94 flammability rating	V-2	Width	27 mm

Classifications

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-37-12-25	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

SwitchMark SM 27/18 MC NE RT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

