

## cable lug, terminal end LIS 2,5M5 V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



### Insulated forked-cable connector made from PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel

#### General ordering data

Type	LIS 2,5M5 V
Order No.	<a href="#">9200380000</a>
Version	cable lug, terminal end, Insulated cable connector, 1.5 mm <sup>2</sup> - 2.5 mm <sup>2</sup> , blue
GTIN (EAN)	4032248410224
Qty.	100 pc(s).

**Data sheet**

**cable lug, terminal end  
LIS 2,5M5 V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	22.9 mm	Width (inches)	0.902 inch
Depth	6.1 mm	Depth (inches)	0.24 inch
Net weight	0.78 g		

**Connectors**

Conductor cross-section, max.	2.5 mm <sup>2</sup>	Conductor cross-section, min.	1.5 mm <sup>2</sup>
Connection density (S1)	0.8 mm	Dimension	M 5
Dimension (bolt)	M 5	Identification colour	blue
Inside diameter (d1)	5.3 mm	Insulation	Available
Material/plastic	PVC	Outside diameter (d)	8.1 mm
Plastic collar diameter (D)	4.5 mm	Plastic collar length (b)	11.3 mm

**Classifications**

ETIM 3.0	EC000494	ETIM 4.0	EC000494
ETIM 5.0	EC001059	ETIM 6.0	EC001059
UNSPSC	41-11-36-37	eClass 5.1	27-20-03-08
eClass 6.2	27-40-02-04	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-12	eClass 9.0	27-40-02-92
eClass 9.1	27-40-02-12		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN</a>

**Data sheet**

**cable lug, terminal end  
LIS 2,5M5 V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

