

**cable lug, terminal end
LIF 2,5F638 RF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Fully-insulated tab-connector sleeves made from
PVC with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 2,5F638 RF
Order No.	9200650000
Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5 mm ² , blue
GTIN (EAN)	4032248410491
Qty.	100 pc(s).

cable lug, terminal end
LIF 2,5F638 RF

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	22 mm	Width (inches)	0.866 inch
Depth	6.3 mm	Depth (inches)	0.248 inch
Net weight	1.25 g		

Connectors

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Dimension	6.3 x 0.8 mm	Dimension (flat blade connector)	6.3 x 0.8 mm
Identification colour	blue	Insulation	Fully insulated
Material/plastic	PVC	Plastic collar diameter (D)	5 mm
Plastic collar length (b)	10.5 mm	Plug-in density (d3)	0.8 mm
Plug-in width (d2)	6.3 mm		

Classifications

ETIM 3.0	EC001509	ETIM 4.0	EC001509
ETIM 5.0	EC001059	ETIM 6.0	EC000516
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	27-40-02-04	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-12	eClass 9.0	27-44-03-92
eClass 9.1	27-40-02-90		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

cable lug, terminal end LIF 2,5F638 RF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

