

**Industrial Ethernet
IE-BS-V01M-SCRJ2SC-SM-C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Bayonet plug-in connector sets according to IEC
61076-3-106 ver.1 (EtherNet/IP), RJ45 metal insert incl.
SC insert

General ordering data

Type	IE-BS-V01M-SCRJ2SC-SM-C
Order No.	1963440000
Version	Flange FO, IP67, Version 1, coupling from SCRJ on 2*SC, Singlemode
GTIN (EAN)	4032248645534
Qty.	10 pc(s).

Industrial Ethernet IE-BS-V01M-SCRJ2SC-SM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight	62.7 g
------------	--------

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Colour	Miscellaneous	Connection 1	SC
Connection 2	SCRJ	Description of article	Version 1, coupling from SCRJ on 2*SC
Fibre type	Singlemode	Housing main material	Zinc diecast
Insertion loss	≤ 0.5 dB	Plugging cycles	500
Protection degree	IP67	Return loss (attenuation)	≥ 40 dB
Seal material	NBR		

Standards

Connector standard	IEC 61076-3-106 Var. 1, IEC 61754-4, IEC 61754-24
--------------------	---

Classifications

ETIM 3.0	EC001121	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC001122
UNSPSC	30-21-18-17	eClass 5.1	27-26-12-03
eClass 6.2	27-26-12-03	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	19-17-01-22
eClass 9.1	19-07-01-22		

Approvals

ROHS	Conform
------	---------

Downloads


Approval/Certificate/Document of Conformity	GOST Approval
Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet IE-BS-V01M-SCRJ2SC-SM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Installation cut-out



Mounting cut-out: 1. With central screw
connection / 2. For mounting with four M3 screws