

**Accessories**  
**TS 35X7.5 2M/CRN****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

The active and passive components as well as the intelligent modules are mounted on terminal rails. Terminal rails are made from stainless steel, steel, aluminium, copper or plastic and are available in diverse types to suit different applications.

**General ordering data**

|            |  |
|------------|--|
| Type       | TS 35X7.5 2M/CRN   |
| Order No.  | <a href="#">1747350000</a>                                       |
| Version    | Mounting rail, DIN EN 60715, Stainless steel, 2000 mm, untreated |
| GTIN (EAN) | 4032248003372  |
| Qty.       | 2 m  |

## Accessories TS 35X7.5 2M/CRN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |          |            |       |
|--------|----------|------------|-------|
| Length | 2,000 mm | Width      | 35 mm |
| Height | 7.5 mm   | Net weight | 354 g |

### Temperatures

|                       |                     |
|-----------------------|---------------------|
| Operating temperature | Storage temperature |
|-----------------------|---------------------|

### Additional technical data

|                     |                 |         |              |
|---------------------|-----------------|---------|--------------|
| Installation advice | Direct mounting | Version | without slot |
|---------------------|-----------------|---------|--------------|

### Dimensions

|              |       |
|--------------|-------|
| TS 35 offset | 10 mm |
|--------------|-------|

### Rated data

|           |              |
|-----------|--------------|
| Standards | DIN EN 60715 |
|-----------|--------------|

### Material data

|                |           |          |                 |
|----------------|-----------|----------|-----------------|
| Surface finish | untreated | Material | Stainless steel |
| Colour         | Grey      |          |                 |

### System specifications

|                |             |               |       |
|----------------|-------------|---------------|-------|
| Product family | Accessories | Mounting rail | TS 35 |
|----------------|-------------|---------------|-------|

### Mounting rail

|   |                    |           |                 |
|---|--------------------|-----------|-----------------|
| Installation advice                             | Direct mounting    | Material  | Stainless steel |
| Short circuit strength corresponds to E-Cu wire | 16 mm <sup>2</sup> | Standards | DIN EN 60715    |
| Surface finish                                  | untreated          | Thickness | 1 mm            |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001285    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-06-04 | eClass 6.2 | 27-14-11-43 |
| eClass 7.1 | 27-14-11-43 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |