

**Accessories**  
**CB 390/4.5 BLACK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

Type	CB 390/4.5 BLACK
Order No.	<a href="#">7940006059</a>
Version	Cable ties, Height x width: 390 x 4.5 mm, Polyamide 66, 220 N
GTIN (EAN)	4032248520367
Qty.	100 pc(s).

## Data sheet

### Accessories CB 390/4.5 BLACK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	4.5 mm	Width (inches)	0.177 inch
Height	390 mm	Height (inches)	15.354 inch
Depth	1.5 mm	Depth (inches)	0.059 inch
Net weight	2.75 g		

### Installation materials

Cable diameter, max.	106 mm	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	UL 94 flammability rating	V-2

### Classifications

ETIM 3.0	EC000046	ETIM 4.0	EC000046
ETIM 5.0	EC000046	ETIM 6.0	EC000046
UNSPSC	30-21-18-01	eClass 5.1	27-14-07-02
eClass 6.2	27-14-07-02	eClass 7.1	27-14-07-02
eClass 8.1	27-14-07-02	eClass 9.0	27-14-07-02
eClass 9.1	27-14-07-02		

### Approvals

Approvals



ROHS Conform

### Downloads

Approval/Certificate/Document of Conformity [DE PI830000160627\\_002](#)  
 Engineering Data [EPLAN, WSCAD](#)

**Data sheet**

**Accessories**  
**CB 390/4.5 BLACK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

