

**RIDERSERIES RCL
RIM 3 110/230VUC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image


Similar to illustration

Pluggable LEDs for the RIDERSERIES RCL relay base with optional protective functions

- With either green or red LED
- With free-wheel diode
- With protective varistor

General ordering data

Type	RIM 3 110/230VUC
Order No.	8691030000
Version	RIDERSERIES RCL, LED module, Rated control voltage: 110...230 V UC, Plug-in connection
GTIN (EAN)	4032248361717
Qty.	10 pc(s).

Data sheet

**RIDERSERIES RCL
RIM 3 110/230VUC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	12.5 mm	Width (inches)	0.492 inch
Height	9 mm	Height (inches)	0.354 inch
Depth	34.5 mm	Depth (inches)	1.358 inch
Net weight	3.041 g		

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	70 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...70 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Rated data UL

Certificate No. (cURus)	E223759
-------------------------	---------

Input

Rated control voltage	110...230 V UC	Status indicator	red LED
-----------------------	----------------	------------------	---------

General data

Colour	black
--------	-------

Further details of approvals / standards

Standards	UL508	Certificate No. (cURus)	E223759
-----------	-------	-------------------------	---------

Connection data

Wire connection method	Plug-in connection
------------------------	--------------------

Classifications

ETIM 3.0	EC000683	ETIM 4.0	EC000996
ETIM 5.0	EC002586	ETIM 6.0	EC002586
UNSPSC	32-11-15-03	eClass 5.1	27-11-06-35
eClass 6.2	27-11-06-35	eClass 7.1	27-37-92-08
eClass 8.1	27-37-92-08	eClass 9.1	27-37-10-10

Approvals

Approvals	
ROHS	Conform

Data sheet

**RIDERSERIES RCL
RIM 3 110/230VUC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com


Technical data

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

**RIDERSERIES RCL
RIM 3 110/230VUC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Wiring diagram****Dimensional drawing**