


Connecting elements H0,75/14D GR SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



- in multi-pack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|--|
| Type | H0,75/14D GR SV |
| Order No. | 9019410000 |
| Version | Wire-end ferrule, insulated, 10 mm, 8 mm, grey |
| GTIN (EAN) | 4008190164096 |
| Qty. | 500 pc(s). |
| Packaging | Multipack bag |

Data sheet

Connecting elements H0,75/14D GR SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|----------------|------------|
| Width | 14 mm | Width (inches) | 0.551 inch |
| Net weight | 0.097 g | | |

Technical data

| | |
|---------|-----------|
| Version | insulated |
|---------|-----------|

Wire-end ferrules

| | | | |
|---|----------------------|-------------------------------|-------------|
| Collar diameter (D2) | 2.8 mm | Colour code | DIN |
| Conductor cross-section | 0.75 mm ² | Contact surface diameter (D1) | 1.2 mm |
| Contact surface length (L2) | 8 mm | L1 in mm | 14 mm |
| Metal sleeve thickness (S1) | 0.15 mm | Military designation | T 20A 005 A |
| Plastic collar thickness (S2) | 0.25 mm | Stripping length | 10 mm |
| Wire connection cross section AWG, max. | AWG 18 | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000005 | ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 | ETIM 6.0 | EC000005 |
| UNSPSC | 31-16-31-02 | eClass 5.1 | 27-40-02-01 |
| eClass 6.2 | 27-40-02-01 | eClass 7.1 | 27-40-02-01 |
| eClass 8.1 | 27-40-02-01 | eClass 9.0 | 27-40-02-01 |
| eClass 9.1 | 27-40-02-01 | | |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Brochure/Catalogue | CAT 6 TOOLS 15/16 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |

Data sheet

**Connecting elements
H0,75/14D GR SV**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

