


Connecting elements H2,5/21T ZH GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in poly-bag
- DIN colour code
- other colour code

General ordering data

Type	H2,5/21T ZH GR
Order No.	9037650000
Version	Wire-end ferrule, Twin wire-end ferrule, 15 mm, 12 mm, grey
GTIN (EAN)	4008190493356
Qty.	100 pc(s).
Packaging	loose

Connecting elements

H2,5/21T ZH GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	21 mm	Width (inches)	0.827 inch
Net weight	0.36 g		

Technical data

Version	Twin wire-end ferrule
---------	-----------------------

Wire-end ferrules

Collar height (A)	8 mm	Collar width (B)	4.5 mm
Colour code	Telemecanique	Conductor cross-section	2.5 mm ²
Contact surface diameter (D1)	2.8 mm	Contact surface length (L2)	12 mm
L1 in mm	21 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.4 mm	Stripping length	15 mm
Wire connection cross section AWG, max.	AWG 14		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Connecting elements H2,5/21T ZH GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

