

**cable lug, terminal end  
LIS 1,5M6 V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



**Insulated forked-cable connector made from PVC  
or PC/PA**

- Conventional designs
- Not soldered
- With conical entry funnel

**General ordering data**

Type	LIS 1,5M6 V
Order No.	<a href="#">9200330000</a>
Version	cable lug, terminal end, Insulated cable connector, 0.5 mm <sup>2</sup> - 1.5 mm <sup>2</sup> , red
GTIN (EAN)	40322484 10156
Qty.	100 pc(s).

**Data sheet**

**cable lug, terminal end  
LIS 1,5M6 V**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	27.9 mm	Width (inches)	1.098 inch
Depth	5.8 mm	Depth (inches)	0.228 inch
Net weight	1.02 g		

**Connectors**

Conductor cross-section, max.	1.5 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Connection density (S1)	0.75 mm	Dimension	M 6
Dimension (bolt)	M 6	Identification colour	red
Inside diameter (d1)	6.4 mm	Insulation	Available
Material/plastic	PVC	Outside diameter (d)	11 mm
Plastic collar diameter (D)	4 mm	Plastic collar length (b)	11.3 mm

**Classifications**

ETIM 3.0	EC001052	ETIM 4.0	EC001052
ETIM 5.0	EC001059	ETIM 6.0	EC001059
UNSPSC	30-21-18-01	eClass 5.1	27-40-02-04
eClass 6.2	27-40-02-04	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-12	eClass 9.0	27-40-02-92
eClass 9.1	27-40-02-12		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN</a>

**Data sheet**

**cable lug, terminal end  
LIS 1,5M6 V**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

