

**cable lug, terminal end
LIF 1,5F488 R****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Insulated tab-connector sleeves made from PVC
with copper sleeve**

- Commercially available designs
- Not soldered
- With conical entry funnel

General ordering data

Type	LIF 1,5F488 R
Order No.	9200530000
Version	cable lug, terminal end, Insulated cable connector, 0.5 mm ² - 1.5 mm ²
GTIN (EAN)	4032248410378
Qty.	100 pc(s).

**cable lug, terminal end
LIF 1,5F488 R**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	19.2 mm	Width (inches)	0.756 inch
Depth	5.7 mm	Depth (inches)	0.224 inch
Net weight	0.71 g		

Connectors

Conductor cross-section, max.	1.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Dimension	4.8 x 0.8 mm	Dimension (flat blade connector)	4.8 x 0.8 mm
Identification colour	red	Insulation	Available
Material/plastic	PVC	Plastic collar diameter (D)	4 mm
Plastic collar length (b)	10 mm	Plug-in density (d3)	0.8 mm
Plug-in width (d2)	4.8 mm		

Classifications

ETIM 3.0	EC001052	ETIM 4.0	EC001052
ETIM 5.0	EC001059	ETIM 6.0	EC000516
UNSPSC	30-21-18-01	eClass 5.1	27-40-02-04
eClass 6.2	27-40-02-04	eClass 7.1	27-40-02-04
eClass 8.1	27-40-02-12	eClass 9.0	27-44-03-92
eClass 9.1	27-40-02-90		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN

cable lug, terminal end LIF 1,5F488 R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

