

**Accessories**  
**TS 35X7.5/LL 1M/ST/ZN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Similar to illustration

**General ordering data**

Type	TS 35X7.5/LL 1M/ST/ZN
Order No.	<a href="#">0514510000</a>
Version	Rail, TS 35, TS 35 x 7.5, with slot, Steel, galvanized, chromium-plated
GTIN (EAN)	4008190116620
Qty.	1 m

**Accessories**  
**TS 35X7.5/LL 1M/ST/ZN**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	35 mm	Width (inches)	1.378 inch
Height	35 mm	Height (inches)	1.378 inch
Depth	7.5 mm	Depth (inches)	0.295 inch
Net weight	314 g		

**Mounting rail**

Drill-hole diameter	5.2 mm	Short circuit strength corresponds to E-Cu wire	16 mm <sup>2</sup>
Slit gap	11 mm	Slit length	25 mm
Slit width	5.2 mm	Slotted drill holes	Yes
Solder eyelet hole diameter (D)	5.2 mm	Spacing of holes, centre-to-centre	36 mm
Thickness	1 mm		

**Classifications**

ETIM 3.0	EC001285	ETIM 4.0	EC001285
ETIM 5.0	EC001285	ETIM 6.0	EC001285
UNSPSC	30-21-18-01	eClass 5.1	27-14-06-04
eClass 6.2	27-14-11-43	eClass 7.1	27-14-11-43
eClass 8.1	27-14-11-43	eClass 9.0	27-40-06-02
eClass 9.1	27-40-06-02		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 4.1 ELECTR 16/17 EN</a> <a href="#">CAT 1 TERM 16/17 EN</a> <a href="#">CAT 2 PORTFOLIOGUIDE EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>