

Electronic housing - EMG 15-LG/SET - 2942975

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Electronic housing set, consisting of electronic housing and printed circuit termination blocks, pitch 5

Product Features

- Choice of four cover sizes in transparent or color versions
- Practical and easy-to-wire conductor connections
- User-friendly and safe mounting on DIN rails according to EN 60715
- Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- High degree of flexibility due to the wide choice of versions
- Uniform and appropriate housing technology
- Inflammability class V0 insulation material (according to UL 94)
- Shock and contamination-proof accommodation of electronic components
- Universal PCBs for all pitches

Key commercial data

package_quantity	10
GTIN	4017918080938

Technical data

General

Housing type	Component housing
Housing material	Polycarbonate fiber reinforced
Color	green

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
--	-------------------

Dimensions

Length	75 mm
Constructional height	47.5 mm
Width	15 mm
Pitch	5 mm

Technical data

Inflammability class according to UL 94	V0
Power dissipation at 20°C in the horizontal mounting position	1.2 W 1.3 W 7.5 mm

Electronic housing - EMG 15-LG/SET - 2942975

Technical data

Technical data

Power dissipation at 20°C in the horizontal mounting position	1.4 W 1.5 W 15 mm
Power dissipation at 20°C in the horizontal mounting position	2 W 2.7 W 52 mm
Number of positions	6

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

accessories

Filler plug


EMG-KA - 2941510



PCB

Electronic housing - EMG 15-LG/SET - 2942975

Dimensioned drawing



Pitch 5 mma = Area for mounting components, 38 mm in the hoodb =
Area for mounting components, 45 mm in the housing

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>