

Cable housing - KGG-MC 1,5/13 - 1834453

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable housing, Pitch: 3.81 mm, Number of positions: 13, Dimension a: 51.92 mm, Color: green

Product Features

- For MC or IMC plugs with and without flange, and 3.81 mm pitch
- Straight cable outlet for sequencing several cable housings
- Incl. transparent label carriers from 6- to 16-pos.
- Easier plug-in and disconnection processes
- Incl. cable binders and marker strips for any numbers of positions
- Full latching of both half shells of the cable housing
- Strain relief for the cables provided by cable binder or a clamp

Key commercial data

| | |
|-------------------------|---------------|
| package_quantity | 10 |
| GTIN | 4017918110796 |

Technical data

Dimensions

| | |
|--------------------|----------|
| Pitch | 3.81 mm |
| Dimension a | 51.92 mm |

General

| | |
|--|------------|
| Range of articles | KGG-MC 1,5 |
| Insulating material group | I |
| Insulating material | ABS |
| Inflammability class according to UL 94 | HB |
| Number of positions | 13 |

classifications

eCl@ss

| | |
|-------------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |

Cable housing - KGG-MC 1,5/13 - 1834453

classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC000879 |
| ETIM 5.0 | EC000451 |



UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11 | 39121409 |
| UNSPSC 12.01 | 39121409 |
| UNSPSC 13.2 | 39121409 |

approvals

GOST / GOST /

Approval details



accessories

Terminal marking

SBS10:UNBEDRUCKT - 1007248



Cable housing - KGG-MC 1,5/13 - 1834453

accessories

KGG-MC 1,5/ DST - 1839050



Drawings

Dimensioned drawing

