

Electrical crimping tool - CF 3000-2,5 - 1205477

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Automatic stripping and crimping device, for insulated taped ferrules 0.25 - 2.5 mm² according to DIN 46228-4: 1990-09

Product Features

- ✔ Thanks to its compact and lightweight design, it can also be used as a portable solution for transport between different work locations
- ✔ The automatic device can be adapted to various cross sections in under a minute
- ✔ Up to 1200 conductors can be processed an hour
- ✔ The compact stripping and crimping machine can be used to process taped ferrules with insulating collars according to DIN 46228-4
- ✔ Color coding according to ferrule standard DIN 46228-4 makes the assignment of modification components really clear
- ✔ The conductor is stripped in a single step and crimped with a ferrule to a high standard of quality
- ✔ Particularly suitable for pre-assembling conductors

Key commercial data

package_quantity	1
GTIN	4017918116910

Technical data

Dimensions

Length (b)	320 mm
Height	300 mm
Width (a)	165 mm

General

Compression	trapezoidal
Type of contact	Ferrules
Min. AWG, flexible, multi-strand	14
AWG max., flexible, multi-strand	24
Working cycle	1.2 s
Power consumption	80 VA
Test standard	DIN 46228-4: 1990-09

classifications

eCl@ss

eCl@ss 4.0	21040301
-------------------	----------

Electrical crimping tool - CF 3000-2,5 - 1205477

classifications

eCl@ss

eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	17130101
eCl@ss 7.0	17130101
eCl@ss 8.0	17130101

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC002778

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

approvals

GOST /

Approval details



accessories

Conversion kit

CF 3000-TOOLKIT 0,25 - 1212376



Sleeve receiver

Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 LOC 0,25 - 1212377



CF 3000 LOC 0,5 - 1205639



CF 3000 LOC 0,75 - 1205642



CF 3000 LOC 1,0 - 1205655



CF 3000 LOC 1,5 - 1205668



CF 3000 LOC 2,5 - 1205671



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 BBE 0,5 - 1205752



CF 3000 BBE 0,75 - 1205765



CF 3000 BBE 1,0 - 1205778



CF 3000 BBE 1,5 - 1205781



CF 3000 BBE 2,5 - 1205794



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 BBE-AME 0,25 - 1207514



CF 3000 BBE-AME 0,5 - 1207488



CF 3000 BBE-AME 0,75 - 1207475



CF 3000 BBE-AME 1,0 - 1207491



CF 3000 BBE-AME 1,5 - 1207501



CF 3000 BBE-AME 2,5 - 1207527



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 CDF 0,25 - 1212389



CF 3000 CG 0,25 - 1212379



CF 3000 CG 0,5 - 1207721



CF 3000 CG 0,75 - 1207734



CF 3000 CG 1,0 - 1207747



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 CG 1,5 - 1207750



CF 3000 CG 2,5 - 1207763



CF 3000 HZG 0,25 - 1212378



CF 3000 HZG 0,5 - 1205684



CF 3000 HZG 0,75 - 1205697



CF 3000 HZG 1,0 - 1205707



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 HZG 1,5 - 1205710



CF 3000 HZG 2,5 - 1205723



Knife

CF 3000 AB 0,25 - 1212380



CF 3000 AM 0,5 - 1205587



CF 3000 AM 0,75 - 1205590



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 AM 1,0 - 1205600



CF 3000 AM 1,5 - 1205613



CF 3000 AM 2,5 - 1205626



CF 3000 AB 0,5 - 1207886



CF 3000 AB 0,75 - 1207899



CF 3000 AB 1,0 - 1207909



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 AB 1,5 - 1207912

CF 3000 AB 2,5 - 1207925



CF 3000 TOOL CASE AB - 3202957

Crimping machine

CF 3000 BEHAELTER - 3202813

CF 3000 CFB 0,25 - 1212392



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 CFT 0,25 - 1212391



CF 3000 KALTGERAETEDOSE - 3202698

CF 3000 KOFFER BESTUECKT - 3202805

CF 3000 REVERSE TASTE - 3202685

CF 3000 SBO - 1205804

CF 3000 SCHWENKARM KOMPL. - 3202766

Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 TRAGEGRIFF - 3202672



CF 3000 ZENTRIERGABEL OBEN - 3202740



CF 3000 ZENTRIERGABEL UNTEN - 3202753

Die

CF 3000 CDM 0,25 - 1212390



CF 3000 CRIMPGESENK - 3202779

Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 CRIMPSTEMPEL - 3202782

Housing

CF 3000 HAUBE - 3202614

Fuse

CF 3000 SI 0,63A/T/250V - 1205736



CF 3000 SI 1,25 A/T/120 V - 1208940



CF 3000 SI 4,0A/T/250V - 1205749



Electrical crimping tool - CF 3000-2,5 - 1205477

accessories

CF 3000 SICHERUNGSHALTER - 3202708

Tool box

CF 3000 TOOL BOX - 1206120

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>