

Electronic housing - ME 17,5 OT-MKDSO KMGY - 2854089

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Housing upper part, for printed circuit terminal block connection

Product Features

- Tool-free mounting
- Low design width with a high number of positions
- Large assembly area
- Same PCB geometry for all design widths
- Recessed labeling areas
- Fast mounting on DIN rails according to EN 60715
- Inflammability class V0 according to UL 94
- Material and part identification embossed on the housing (recyclability)
- Cost savings thanks to easy device production
- Electronic components can be partially removed
- Functional earth ground contact (EMC) integrated in the housing base
- Optional BUS connection integrated in the housing, for either parallel or serial contacting
- Metal foot catch

Key commercial data

package_quantity	10
GTIN	4017918458973

Technical data

General

Housing type	Upper part
Housing material	Polyamide
Color	light gray

Dimensions

Constructional height	38.5 mm
Width	17.5 mm

Technical data

Inflammability class according to UL 94	V0
Number of positions	24
Number of positions	36

Electronic housing - ME 17,5 OT-MKDSO KMGY - 2854089

Technical data

Technical data

Number of positions	12
---------------------	----

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27141190
eCl@ss 6.0	27141190
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized /

Approval details



accessories

Mounting material

Electronic housing - ME 17,5 OT-MKDSO KMGY - 2854089

accessories

ME DH36 NS 35 - 2909895



ME DH27 NS 35 - 2908760



ME-SAS - 2853899



Component housing upper part

ME 17,5 OT-MKDSO KMGY - 2854089



Printed circuit board terminal

MKDSO 2,5/ 3-R KMGY - 2854092



Electronic housing - ME 17,5 OT-MKDSO KMGY - 2854089

accessories

MKDSO 2,5/ 3-L KMGY - 2854102



Printed circuit board housing

MSTBO 2,5/ 3-G1L KMGY - 2853750



MSTBO 2,5/ 3-G1R KMGY - 2853763



Filler plug

ME B-SA/NS 35 - 2935959



ME B-KA - 2854173



Electronic housing - ME 17,5 OT-MKDSO KMGY - 2854089

accessories

ME B-17,5 MKDSO KMGY - 2854115



ME B-17,5 MSTBO KMGY - 2853776



ME B-SA/NS 35 - 2935959



ME B-KA - 2854173



PCB plug

FKCT 2,5/ 3-ST - 1909223



Electronic housing - ME 17,5 OT-MKDSO KMGY - 2854089

accessories

MSTBT 2,5/ 3-ST KMGY - 1971947



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>