

Voltage tester - DUSPOL EXPERT - 1209091

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1100 V DC, IP65

Product Features

- Audible and optical continuity test
- Surge voltage category CAT IV 600 V and CAT III 1000 V according to IEC/EN 61243-3
- Vibration alarm for safe voltage detection
- Shock-proof, dust-proof, and splash-proof housing, IP64
- DC and AC voltage tests in the range from 12 V to 690 V AC/750 V DC, fully functional even without batteries
- Polarity test (+/-) for DC voltage
- Single-pos. test of the phase conductor
- Indicator for the direction of rotating field of a three-phase network as long as the star point is grounded
- Measuring point lighting
- Load connection via pushbutton

Key commercial data

package_quantity	1
GTIN	4046356309905

Technical data

Ambient conditions

Ambient temperature (operation)	-10 °C ... 55 °C
Degree of protection	IP65

General

Color	black
Voltage supply	2 x micro battery 1.5 V, LR03, AAA
Measuring category	CAT IV 600 V/CAT III 1000V
Test certificate	EN/IEC 61243-3 (VDE 0682 Part 401)
Display scope	12 V, 24 V, 50 V, 120 V, 230 V, 400 V, 690 V, 1000 V LED diode display
Phase-sequence indicator	LCD (symbol "R")
Phase display	LCD (symbol "R")
Polarity display	LED (symbol "+/-")
Measuring point lighting	LED
Innenwiderstand_Messkreis	220.00 kΩ

Voltage tester - DUSPOL EXPERT - 1209091

Technical data

General

Innenwiderstand_Lastkreis	3.70 kΩ
Minimum voltage	12 V DC
Max. voltage	1100 V DC
Minimum voltage	12 V AC
Max. voltage	1000 V AC

classifications

eCl@ss

eCl@ss 4.0	27200312
eCl@ss 4.1	27200301
eCl@ss 5.0	27200301
eCl@ss 5.1	27200301
eCl@ss 6.0	27200301
eCl@ss 7.0	27200301
eCl@ss 8.0	27200301

ETIM

ETIM 2.0	EC000149
ETIM 3.0	EC000149
ETIM 4.0	EC000494
ETIM 5.0	EC000494

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GOST / VDE Zeichengenehmigung /

Approval details



Voltage tester - DUSPOL EXPERT - 1209091

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>