

# Crimping pliers - CRIMPFOX-RC 25 - 1212065

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Crimping pliers, for non-insulated cable lugs, 10 - 25 mm<sup>2</sup>, indent crimp

## Product Features

- CRIMPFOX-RC 10 and ...RCT 25-1 complete the range of crimping pliers for uninsulated cable lugs and insulated tube lugs
- All pliers of this type reduce the amount of force required during crimping by 25%



## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356454056

## Technical data

### Dimensions

<b>Length (b)</b>	256 mm
<b>Height</b>	68 mm
<b>Width (a)</b>	25 mm

### General

<b>Color</b>	black
<b>Compression</b>	Indent crimp
<b>Type of contact</b>	Non-insulated cable lugs
<b>Name</b>	Crimping position 1
<b>Max. cross section</b>	10 mm <sup>2</sup>
<b>AWG max</b>	8
<b>Name</b>	Crimping position 2
<b>Max. cross section</b>	16 mm <sup>2</sup>
<b>AWG max</b>	6
<b>Name</b>	Crimping position 3
<b>Max. cross section</b>	25 mm <sup>2</sup>
<b>AWG max</b>	4
<b>Die station</b>	Crimping position 4
<b>Die station</b>	Crimping position 5

# Crimping pliers - CRIMPFOX-RC 25 - 1212065

## classifications

### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## approvals

GOST /

### Approval details



## accessories

### Die

CRIMPFOX-RC 25/DIE - 1212299



## Mounting material

# Crimping pliers - CRIMPFOX-RC 25 - 1212065

accessories

CRIMPFOX/ SPR-1 - 1212069



---

## Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>