

Cutting tool - PPS STANDARD M - 1206175

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Profile cutter, for cutting and stamping holes in standard DIN rails, NS 15 / NS 32 / NS 35/7,5 / NS 35/15, and for cutting the NLS-CU 3/10 neutral busbar to length, can accommodate 2 stamping bits, with metric measuring rail, supplied without stamping bits

Key commercial data

package_quantity	1
GTIN	4017918163280

Technical data

Dimensions

Length (b)	100 mm
Height	220 mm
Width (a)	180 mm
Length of the measuring bar	1000 mm

General

Color	black
Type	Millimeter

classifications

eCl@ss

eCl@ss 4.0	21040302
eCl@ss 4.1	21040302
eCl@ss 5.0	21040302
eCl@ss 5.1	21040302
eCl@ss 6.0	21049190
eCl@ss 7.0	21049190
eCl@ss 8.0	21049190

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000385
ETIM 5.0	EC000385

UNSPSC

Cutting tool - PPS STANDARD M - 1206175

classifications

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	23171604

approvals

GOST /

Approval details

GOST

accessories

Conversion kit

PPS-ST (3,5X12)L - 1203563



PPS-ST (4,5X12)L - 1203534



PPS-ST (5,5X12)L - 1202603



Cutting tool - PPS STANDARD M - 1206175

accessories

PPS-ST (6,35X15)L - 1204876



PPS-ST (6,5X15)L - 1202593



PPS-ST (3,5X12)Q - 1203550



PPS-ST (4,5X12)Q - 1203547



PPS-ST (5,5X12)Q - 1203411



PPS-ST (6,5X15)Q - 1203408



Cutting tool - PPS STANDARD M - 1206175

accessories

PPS-ST (3,8) - 1204892



PPS-ST (4,3) - 1202616



PPS-ST (5,3) - 1202629



PPS-ST (6,4) - 1202632



PPS-ST (7,0) - 1204889



Cutting tool - PPS STANDARD M - 1206175

accessories

PPS-ST (8,4) - 1202726



Profile cutters

PPS TABLE - 1206285



Universal tools

PPS HYDRAULIC CYL - 1208924



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>