

Economy Fixed Wall Mount Cabinet *RB-FW Series*

130 lbs Weight Capacity

Features



- Constructed in light duty 16-gauge steel.
- Includes two (2) pairs of EIA-310-D compliant 19 inch square hole mounting rails.
 - Starter pack of (25) M6 screws, cage nuts and washers included.
 - For 10-32 hardware see the **CAGKIT Series**.
- Rails are adjustable.
- Includes one (1) tempered glass lightly smoked reversible front door.
- Includes one (1) pair of locking removable side panels.
- Front and side of frame includes venting for air flow.
- Rear cable access.
- Provision for optional fans on top panel.
- Ships un-assembled - some assembly required.
- Finished in black powder paint.
- Tested to 130 lbs (59 kg) of equipment load capacity.
- RoHS Compliant.



Part of the Rack Basics® line of economy rack solutions.


Accessories

- Horizontal Ring Cable Manager
- Horizontal Lacing Strip
- Outlet Strips
- Mounting Hardware
- Universal Rack Shelf
- Cable Lacing Bar
- Grill Fan Kits



| Part No. | Overall Dimensions | | | Mounting Dimensions | | | Usable Depth | Rack Units |
|----------|--------------------|-------|-------|---------------------|-------|-------|--------------|------------|
| | Height | Width | Depth | Height | Width | Depth | | |
| RB-FW6 | 14.65 | 23.62 | 23.62 | 10.50 | 19.00 | 16.93 | 21.24 | 6U |
| RB-FW9 | 19.90 | 23.62 | 23.62 | 15.75 | 19.00 | 16.93 | 21.24 | 9U |
| RB-FW12 | 25.15 | 23.62 | 23.62 | 21.00 | 19.00 | 16.93 | 21.24 | 12U |
| RB-FW15 | 30.40 | 23.62 | 23.62 | 26.25 | 19.00 | 16.93 | 21.24 | 15U |

Note: Usable depth is the furthest depth equipment can be mounted in the cabinet.


Data subject to change without notice




TOP VIEW




REAR VIEW




FRONT VIEW DOOR REMOVED



R.S VIEW



TOP VIEW PANEL REMOVED



BOTTOM VIEW

| PART NUMBERS | |
|--|------------------------|
| RB-FW12 | PAINTED BLACK TEXTURED |
| NOTES | |
| HARDWARE INCLUDED. SHIPS KNOCKED DOWN. | |
| Français | |
| Pour tous les détails sur nos produits, svp veuillez consulter notre site www.hammondmfg.com | |

Data subject to change without notice. Isometric drawing not to scale.
Les données sont sujettes à changement sans préavis.



www.hammondmfg.com

PART NO. RB-FW12