


Data sheet | Item number: 286-111

Empty component plug housing; Type 10; 15 mm wide; 6-pole

[www.wago.com/286-111](http://www.wago.com/286-111)



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color: ■

### Item description

Empty component plug housing, type 10

### Data

#### Electrical data

Rated continuous current

6 A

## Safety and protection:

Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3

## Connection data

No. of poles	6
--------------	---

## Geometrical Data

Width	15 mm / 0.591 inch
Height from upper-edge of DIN-35 rail	82.5 mm / 3.243 inch

## Mechanical data

Housing design	Pluggable module for terminal blocks
Type of mounting	Pluggable module for carrier terminal blocks

## Material Data

Color	gray
Fire load	0.315 MJ
Weight	14.486 g

## Commercial data

Country of origin	DE
GTIN	4044918840101
Customs Tariff No.	85472000900
Product Group	6 (Interface Electronics)

## Compatible products

### tools



**Item no.: 210-492**  
Unlocking pliers for component plug housing

[www.wago.com/210-492](http://www.wago.com/210-492)

### General accessories



**Item no.: 280-609**  
Terminal block for pluggable modules; 12-pole; with 4-conductor terminal blocks; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>

[www.wago.com/280-609](http://www.wago.com/280-609)



**Item no.: 280-619**  
Terminal block for pluggable modules; 6-pole; with 2-conductor terminal blocks; with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>

[www.wago.com/280-619](http://www.wago.com/280-619)

**Item no.: 280-763**  
Terminal block for pluggable modules; 12-pole; with 4-conductor terminal blocks; with marker carrier;

[www.wago.com/280-763](http://www.wago.com/280-763)



with orange separator; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm<sup>2</sup>

**Marking accessories**



**Item no.: 209-701**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701](http://www.wago.com/209-701)



**Item no.: 209-701/000-002**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-002](http://www.wago.com/209-701/000-002)



**Item no.: 209-701/000-005**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-005](http://www.wago.com/209-701/000-005)



**Item no.: 209-701/000-006**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-006](http://www.wago.com/209-701/000-006)



**Item no.: 209-701/000-007**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-007](http://www.wago.com/209-701/000-007)



**Item no.: 209-701/000-012**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-012](http://www.wago.com/209-701/000-012)



**Item no.: 209-701/000-017**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-017](http://www.wago.com/209-701/000-017)



**Item no.: 209-701/000-023**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-023](http://www.wago.com/209-701/000-023)



**Item no.: 209-701/000-024**  
WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/209-701/000-024](http://www.wago.com/209-701/000-024)

**Downloads**

**Documentation**

**Additional Information**

Disposal; Electrical and electronic equipment, Packaging

Oct 15, 2018

[Download](#)  
265.8 kB

**smartDATA**

**CAD data**

3D Download 286-111

[URL](#) [Download](#)



Subject to changes.

---

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.