

# Adapter cable - CABLE-15/8/250/RSM/INDRADYN-2 - 2986986

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable adapter for PSR speed monitors (PSR-RSM4 and PSR-MOTIONSTOP), cable length: 2.5 m, for controller: Bosch Rexroth Indramat, type: IndraDrive - IndraDyn

## Product Features

- Option to connect to PSR-RSM4 and PSR-MOTIONSTOP safe speed monitors
- Suitable for connection to the existing motor feedback interface of an electrical drive
- Controller type: REXROTH
- 15-pos. D-SUB connection
- Length of connecting cable to speed monitor: 250 cm

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356477222

## Technical data

### Dimensions

<b>Fixed cable length</b>	2.5 m
---------------------------	-------

### Ambient conditions

<b>Ambient temperature (operation)</b>	-20 °C ... 60 °C (for fixed installation)
<b>Ambient temperature (operation)</b>	0 °C ... 50 °C (for flexible installation)
<b>Ambient temperature (storage/transport)</b>	-20 °C ... 70 °C

### General

<b>Connection 1</b>	To the device
<b>Connection method</b>	RJ45
<b>Connection method</b>	D-SUB-15 male/D-SUB-15 female
<b>Number of positions</b>	15
<b>Cable resistance</b>	≤ 260 Ω/km
<b>Conductor material</b>	Bare Cu litz wires
<b>Shielding</b>	Plastic-coated aluminum foil, tinned copper braided shield
<b>Shielding</b>	Soldering on D-SUB housing
<b>Conductor cross section</b>	0.48 mm <sup>2</sup> (AWG 26)

## Adapter cable - CABLE-15/8/250/RSM/INDRADYN-2 - 2986986

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	27060307
<b>eCl@ss 4.1</b>	27060307
<b>eCl@ss 5.0</b>	27060307
<b>eCl@ss 5.1</b>	27060307
<b>eCl@ss 6.0</b>	27060307
<b>eCl@ss 7.0</b>	27060307
<b>eCl@ss 8.0</b>	27060307

#### ETIM

<b>ETIM 3.0</b>	EC000467
<b>ETIM 4.0</b>	EC000467
<b>ETIM 5.0</b>	EC000467

#### UNSPSC

<b>UNSPSC 6.01</b>	30211901
<b>UNSPSC 7.0901</b>	39121501
<b>UNSPSC 11</b>	39121501
<b>UNSPSC 12.01</b>	39121501
<b>UNSPSC 13.2</b>	39121501

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>