


Data sheet | Item number: 280-803/281-413
LED module; with red LED; 10 mm wide; 24 VDC

www.wago.com/280-803/281-413





Data

Electrical data

Voltage type (1)	DC
------------------	----

Ratings per IEC/EN 60664-1

Rated current	0.025 A
---------------	---------

Geometrical Data

Width	10 mm / 0.394 inch
-------	--------------------

Plug width	10 mm / 0.394 inch
------------	--------------------

Material Data

Color	gray
-------	------

Insulating material	Polyamide 66 (PA 66)
---------------------	----------------------

Fire load	0.074 MJ
-----------	----------

Weight	4.232 g
--------	---------

Commercial data

Country of origin	DE
-------------------	----

GTIN	4045454396602
------	---------------

Customs Tariff No.	85369010000
--------------------	-------------

Product Group	1 (Rail Mounted Terminal Blocks)
---------------	----------------------------------

Compatible products

clamps



Item no.: 280-101

2-conductor through terminal block; 2.5 mm²; lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5;
CAGE CLAMP®

www.wago.com/280-101



Item no.: 280-601

2-conductor through terminal block; 2.5 mm²; lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

www.wago.com/280-601



Item no.: 280-603

4-conductor through terminal block; 2.5 mm²; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

www.wago.com/280-603



Item no.: 280-621

4-conductor through terminal block; 2.5 mm²; lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

www.wago.com/280-621



Item no.: 280-633

4-conductor through terminal block; 2.5 mm²; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

www.wago.com/280-633



Item no.: 280-681

3-conductor through terminal block; 2.5 mm²; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®


www.wago.com/280-681



Item no.: 280-833

4-conductor through terminal block; 2.5 mm²; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

www.wago.com/280-833



Item no.: 280-901

2-conductor through terminal block; 2.5 mm²; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

www.wago.com/280-901

Downloads

Documentation

Bid Text

280-803/281-413	Oct 12, 2017	DOC 23.6 kB	Download
-----------------	--------------	----------------	----------

smartDATA

CAD data

3D Download 280-803/281-413	URL	Download
-----------------------------	-----	----------

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.