



Data sheet | Item number: 280-850/281-413

Fuse plug; 5 mm wide; with soldered miniature fuse; with additional indicator lamp; red LED; DC 15 - 30 V; 250 mA FF



[www.wago.com/280-850/281-413](http://www.wago.com/280-850/281-413)





## Data

### Electrical data

#### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	125 V
Rated current	5 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

### Geometrical Data

Width	5 mm / 0.197 inch
Plug width	5 mm / 0.197 inch

### Mechanical data

Marking level	without marking level
---------------	-----------------------

### Material Data

Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load	0.053 MJ
Weight	2.872 g

### Commercial data

Country of origin	DE
GTIN	4045454363086
Customs Tariff No.	85366990990

Product Group


1 (Rail Mounted Terminal Blocks)

## Approvals / Certificates

### Country specific Approvals






Logo	Approval	Certificate name
	CCA DEKRA Certification B.V.	2160584.53

### Ship Approvals

Logo	Approval	Certificate name
	ABS American Bureau of Shipping	14-HG1293677-PDA

## Compatible products

### clamps

	<b>Item no.: 280-610</b> 3-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-610">www.wago.com/280-610</a>
	<b>Item no.: 280-616</b> 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-616">www.wago.com/280-616</a>
	<b>Item no.: 280-686</b> 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-686">www.wago.com/280-686</a>
	<b>Item no.: 280-816</b> 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-816">www.wago.com/280-816</a>
	<b>Item no.: 280-916</b> 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm <sup>2</sup> ; CAGE CLAMP®	<a href="http://www.wago.com/280-916">www.wago.com/280-916</a>

## Downloads

### Documentation

#### Bid Text

280-850/281-413	Oct 12, 2017	DOC 24.6 kB	Download
-----------------	--------------	----------------	----------



Subject to changes.

---

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.