



Data sheet | Item number: 280-803/281-420

Diode module; with 1N4007 recovery diode; red LED; 10 mm wide; 24 VDC



[www.wago.com/280-803/281-420](http://www.wago.com/280-803/281-420)



## Data

### Electrical data

Nominal voltage	250 V
Reverse voltage	1000 V

## Ratings per IEC/EN 60664-1

Rated current	0.5 A
---------------	-------

## Geometrical Data

Width	10 mm / 0.394 inch
Plug width	10 mm / 0.394 inch

## Material Data








Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load	0.089 MJ
Weight	4.632 g

## Commercial data

Country of origin	DE
GTIN	4050821864974
Customs Tariff No.	85369010000

## Compatible products

## clamps

	<b>Item no.: 280-101</b> 2-conductor through terminal block; 2.5 mm <sup>2</sup> ; lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-101">www.wago.com/280-101</a>
	<b>Item no.: 280-601</b> 2-conductor through terminal block; 2.5 mm <sup>2</sup> ; lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-601">www.wago.com/280-601</a>
	<b>Item no.: 280-603</b> 4-conductor through terminal block; 2.5 mm <sup>2</sup> ; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-603">www.wago.com/280-603</a>
	<b>Item no.: 280-621</b> 4-conductor through terminal block; 2.5 mm <sup>2</sup> ; lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-621">www.wago.com/280-621</a>
	<b>Item no.: 280-633</b> 4-conductor through terminal block; 2.5 mm <sup>2</sup> ; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-633">www.wago.com/280-633</a>
	<b>Item no.: 280-681</b> 3-conductor through terminal block; 2.5 mm <sup>2</sup> ; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-681">www.wago.com/280-681</a>
	<b>Item no.: 280-833</b> 4-conductor through terminal block; 2.5 mm <sup>2</sup> ; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-833">www.wago.com/280-833</a>
	<b>Item no.: 280-901</b> 2-conductor through terminal block; 2.5 mm <sup>2</sup> ; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®	<a href="http://www.wago.com/280-901">www.wago.com/280-901</a>



CLAMP®

---

## Downloads

### Documentation

#### Bid Text

280-803/281-420	Oct 12, 2017	DOC 24.1 kB	Download
-----------------	--------------	----------------	----------

---

## smartDATA

### CAD data

3D Download 280-803/281-420	URL	Download
-----------------------------	-----	----------

Subject to changes.