


Data sheet | Item number: 281-512

Fuse plug with pull-tab; for miniature metric fuses 5 x 20 mm and 5 x 25 mm;
with hole for one led (for self-assembly); 6 mm wide




www.wago.com/281-512



RoHS
Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:



Data

Electrical data

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	250 V
Rated current	6.3 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

Geometrical Data

Width	6 mm / 0.236 inch
Plug width	6 mm / 0.236 inch

Mechanical data

Marking level	Center marking
---------------	----------------

Material Data

Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load	0.076 MJ
Weight	6.13 g

Commercial data



Country of origin	CN
GTIN	4050821032557
Customs Tariff No.	85366990990
Product Group	1 (Rail Mounted Terminal Blocks)

Approvals / Certificates

Country specific Approvals

Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	1505034
	CSA DEKRA Certification B.V.	1505034

Ship Approvals




Logo	Approval	Certificate name
	ABS American Bureau of Shipping	14-HG1293677-PDA
	ABS American Bureau of Shipping	14-HG1293677-PDA
















UL-Approvals

Logo	Approval	Certificate name
	UL Underwriters Laboratories Inc.	E45172

Compatible products

Marking accessories

	Item no.: 2009-114 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	www.wago.com/2009-114
	Item no.: 2009-114/000-002 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	www.wago.com/2009-114/000-002
	Item no.: 2009-114/000-005 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	www.wago.com/2009-114/000-005

	<p>Item no.: 2009-114/000-006 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-006
	<p>Item no.: 2009-114/000-007 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-007
	<p>Item no.: 2009-114/000-012 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-012
	<p>Item no.: 2009-114/000-023 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-023
	<p>Item no.: 2009-114/000-024 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-024
	<p>Item no.: 209-701 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701
	<p>Item no.: 209-701/000-002 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-002
	<p>Item no.: 209-701/000-005 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-005
	<p>Item no.: 209-701/000-006 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-006
	<p>Item no.: 209-701/000-007 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-007
	<p>Item no.: 209-701/000-012 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-012
	<p>Item no.: 209-701/000-017 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-017
	<p>Item no.: 209-701/000-023 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-023
	<p>Item no.: 209-701/000-024 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-024
	<p>Item no.: 793-4501 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/793-4501



Item no.: 793-4501/000-002
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-002



Item no.: 793-4501/000-005
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-005



Item no.: 793-4501/000-006
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-006



Item no.: 793-4501/000-007
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-007



Item no.: 793-4501/000-012
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-012



Item no.: 793-4501/000-014
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-014



Item no.: 793-4501/000-023
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-023



Item no.: 793-4501/000-024
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type


www.wago.com/793-4501/000-024

General accessories




Item no.: 281-503
Shorting link; 5 x 20 mm; if the fuse plug is used as disconnect plug

www.wago.com/281-503



Item no.: 281-610
3-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm²; CAGE CLAMP®

www.wago.com/281-610



Item no.: 281-656
4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm²; CAGE CLAMP®

www.wago.com/281-656



Item no.: 281-916
2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm²; CAGE CLAMP®

www.wago.com/281-916

clamps



Item no.: 280-510
Triple-deck terminal block

www.wago.com/280-510



Item no.: 280-514
Double-deck terminal block

www.wago.com/280-514



Item no.: 280-528
Double-deck terminal block

www.wago.com/280-528

Item no.: 280-531



Double-deck terminal block

www.wago.com/280-531



Item no.: 280-532
Double-deck terminal block

www.wago.com/280-532



Item no.: 280-889
Triple-deck terminal block

www.wago.com/280-889



Item no.: 280-891
Double-deck terminal block

www.wago.com/280-891

Downloads

Documentation

Bid Text

281-512	Oct 12, 2017	DOC 24.6 kB	Download
---------	--------------	----------------	----------

smartDATA

CAD data

3D Download 281-512	URL	Download
---------------------	-----	----------

Subject to changes.