


Data sheet | Item number: 281-512/281-418

Fuse plug with pull-tab; for miniature metric fuses 5 x 20 mm and 5 x 25 mm;
with neon lamp, 120 V AC/DC; 6 mm wide



www.wago.com/281-512/281-418



RoHS 
Compliant

BOMcheck.net

Color: **Data****Electrical data**

Voltage type (1) AC/DC

Ratings per IEC/EN 60664-1

Rated voltage (III / 3) 250 V

Rated current 6.3 A

Legend (ratings) (III / 3) \triangleq Overvoltage category III / Pollution degree 3**Geometrical Data**

Width 6 mm / 0.236 inch

Plug width 6 mm / 0.236 inch

Mechanical data

Marking level Center marking

Material Data

Color gray

Insulating material Polyamide 66 (PA 66)

Fire load 0.082 MJ

Weight 6.351 g

Commercial data

Country of origin CN

GTIN 4050821276258

Customs Tariff No. 85366990990



Product Group 1 (Rail Mounted Terminal Blocks)

Approvals / Certificates**Country specific Approvals**

Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	1505034
	CSA	1505034

DEKRA Certification B.V.

Ship Approvals





Logo	Approval	Certificate name
	ABS American Bureau of Shipping	14-HG1293677-PDA
	ABS American Bureau of Shipping	14-HG1293677-PDA

UL-Approvals





Logo	Approval	Certificate name
	UL Underwriters Laboratories Inc.	E45172
















Compatible products

General accessories

	Item no.: 281-503 Shorting link; 5 x 20 mm; if the fuse plug is used as disconnect plug	www.wago.com/281-503
	Item no.: 281-610 3-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm ² ; CAGE CLAMP®	www.wago.com/281-610
	Item no.: 281-656 4-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm ² ; CAGE CLAMP®	www.wago.com/281-656
	Item no.: 281-916 2-conductor carrier terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 4 mm ² ; CAGE CLAMP®	www.wago.com/281-916

Marking accessories

	Item no.: 2009-114 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	www.wago.com/2009-114
	Item no.: 2009-114/000-002 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	www.wago.com/2009-114/000-002
	Item no.: 2009-114/000-005 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	www.wago.com/2009-114/000-005
	Item no.: 2009-114/000-006 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	www.wago.com/2009-114/000-006

	<p>Item no.: 2009-114/000-007 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-007
	<p>Item no.: 2009-114/000-012 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-012
	<p>Item no.: 2009-114/000-023 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-023
	<p>Item no.: 2009-114/000-024 WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/2009-114/000-024
	<p>Item no.: 209-701 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701
	<p>Item no.: 209-701/000-002 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-002
	<p>Item no.: 209-701/000-005 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-005
	<p>Item no.: 209-701/000-006 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-006
	<p>Item no.: 209-701/000-007 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-007
	<p>Item no.: 209-701/000-012 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-012
	<p>Item no.: 209-701/000-017 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-017
	<p>Item no.: 209-701/000-023 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-023
	<p>Item no.: 209-701/000-024 WSB marking card; as card; not stretchable; plain; snap-on type</p>	www.wago.com/209-701/000-024
	<p>Item no.: 793-4501 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/793-4501
	<p>Item no.: 793-4501/000-002 WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type</p>	www.wago.com/793-4501/000-002



Item no.: 793-4501/000-005
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-005



Item no.: 793-4501/000-006
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-006



Item no.: 793-4501/000-007
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-007



Item no.: 793-4501/000-012
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-012



Item no.: 793-4501/000-014
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-014



Item no.: 793-4501/000-023
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-023



Item no.: 793-4501/000-024
WMB marking card; as card; stretchable 4 - 4.2 mm; plain; snap-on type

www.wago.com/793-4501/000-024

clamps



Item no.: 280-510
Triple-deck terminal block

www.wago.com/280-510



Item no.: 280-514
Double-deck terminal block

www.wago.com/280-514



Item no.: 280-528
Double-deck terminal block

www.wago.com/280-528



Item no.: 280-531
Double-deck terminal block

www.wago.com/280-531



Item no.: 280-532
Double-deck terminal block

www.wago.com/280-532



Item no.: 280-889
Triple-deck terminal block

www.wago.com/280-889



Item no.: 280-891
Double-deck terminal block

www.wago.com/280-891

Downloads

Documentation

Bid Text



281-512/281-418

Oct 12, 2017

DOC
24.6 kB

Download

smartDATA

CAD data

3D Download 281-512/281-418

URL

Download

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.