

# Vulcascot Rubber Cable Protector Product Availability

- Prevents accidents caused by loose leads and cables.
- Low smoke, non toxic and a low fume emission level in the event of fire.
- UV stabilised for extended outdoor life.


- Fire retardant to BS 476 PART 7 Class 3 and European equivalent DIN 4102 PART 1 and Class B1.
- Tested for non conductivity to BS 903-C5 500V.

## SNAP TOP®

Seven configurations designed primarily for telecommunication applications.

Colour - grey.

Length - 9 metres.




## SNAP FIT®

Nine profiles to house most general purpose cables and leads in office use.

Colours - black, grey or beige.

Length - 9 metres.




## INDUSTRIAL

Five sections for industrial indoor and outdoor applications.

Colours - black or grey.


Length - Types A and F 9 metre coils. Types FF and FFF 4.5 metre coils.




Dimensions are for reference only.

## WARNING PROFILES

TYPE 1



TYPE 2




## TEMPORARY TRAFFIC CALMERS

TYPE TTC / 1



TYPE TTC / 2



TYPE TTC / 3



Website: [www.vulcascot.com](http://www.vulcascot.com)  
E-mail: [vulcascot.baz@btinternet.com](mailto:vulcascot.baz@btinternet.com)

# Flexible Cable Protector

pb Artikelnr.	Profile	Colour	Length	Base Width	Height	Packed weight
VUS-001	Snap Fit type Standard	Black	3m	68mm	11mm	3,5kg
VUS-002	Snap Fit type Standard	Grey	3m	68mm	11mm	3,5kg
VUS-003	Snap Fit type B	Black	3m	83mm	14mm	3,8kg
VUS-004	Snap Fit type B	Grey	3m	83mm	14mm	3,8kg
VUS-005	Snap Fit type E	Black	3m	73mm	14mm	3,2kg
VUS-006	Snap Fit type E	Grey	3m	73mm	14mm	3,2kg
VUS-007	Snap Fit type BNC1	Black	3m	83mm	14mm	3,2kg
VUS-008	Snap Fit type BNC1	Grey	3m	83mm	14mm	3,2kg
VUS-009	Snap Fit type BNC2	Black	3m	88mm	14mm	3,4kg
VUS-010	Snap Fit type BNC2	Grey	3m	88mm	14mm	3,4kg
VUS-011	Snap Fit type BNC3	Black	4,5m	108mm	14mm	5,6kg
VUS-012	Snap Fit type BNC3	Grey	4,5m	108mm	14mm	5,6kg
VUS-013	New Multi Compartment MCP/1	Black	3m	83mm	20mm	3,8kg
VUS-014	New Multi Compartment MCP/1	Grey	3m	83mm	20mm	3,8kg
VUS-015	New Multi Compartment MCP/2	Black	3m	120mm	24mm	9,4kg
VUS-016	New Multi Compartment MCP/2	Grey	3m	120mm	24mm	9,4kg
VUS-017	Warning Profile type HAZ/1	Balck/yellow	3m	68mm	15mm	3,5kg
VUS-018	Warning Profile type HAZ/2	Balck/yellow	3m	83mm	16mm	3,8kg
VUS-019	Warning Profile type DAN/1	Gray/red	3m	68mm	15mm	3,5kg
VUS-020	Warning Profile type DAN/2	Gray/red	3m	83mm	16mm	3,8kg



fastener & components

